

## Proposed UPS system



Quantity **UPS**  
1 PowerValue 11 RT 10 kVA  
Order-Code: 4NWP100104R0001

Quantity **Battery module**  
0 PowerValue 11 RT EBM 10 kVA  
Order-Code: 4NWP100109R0001

### Product overview

<b>System description</b>	PowerValue 11 RT 10 kVA + 0x PowerValue 11 RT EBM 10 kVA
<b>Order code</b>	4NWP100104R0001 + 0x 4NWP100109R0001
<b>UPS rated power</b>	10000 VA, 9000 W
<b>UPS type</b>	Online Double Conversion
<b>Efficiency</b>	93.0% (@100% nominal load)
<b>Internal battery</b>	N.A.
<b>Battery module</b>	0 pcs
<b>System runtime</b>	90% load, 0 min 100% load, 0 min

Dimensions	Product description	Weight (kg)	Width (mm)	Height (mm)	Depth (mm)	
<b>UPS</b>	PowerValue 11 RT 10 kVA	28.1	438	215.5	594	
<b>Battery module</b>	PowerValue 11 RT EBM 10 kVA	62.5	438	129	594	
Package dimensions	Product description	Smallest sales unit	Weight (kg)	Width (mm)	Height (mm)	Depth (mm)
<b>UPS</b>	PowerValue 11 RT 10 kVA	1	30.8	560	340	860
<b>Battery module</b>	PowerValue 11 RT EBM 10 kVA	1	65.9	580	350	790